



FMT MicroVAM Fiber Optic Module, CWDM, 4 channels, mux/demux, LC /UPC, starting wavelength 1611 nm, 1310 nm upgrade port

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	CWDM module
<b>Product Series</b>	FMT

## General Specifications

<b>Device Type</b>	Micro VAM
<b>Functionality</b>	Demultiplexing   Multiplexing
<b>Access</b>	Front
<b>Application</b>	For use with FMT panels   For use with NGF frames
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	4-channel CWDM
<b>Interface, front</b>	LC/UPC
<b>Interface, Input</b>	LC/UPC
<b>Interface Feature, Input</b>	Standard
<b>Interface, Output</b>	LC/UPC
<b>Interface Feature, Output</b>	Standard
<b>Multiplexers, quantity</b>	1
<b>Port Type, optional</b>	Upgrade port

## Dimensions

<b>Height</b>	71.88 mm   2.83 in
<b>Width</b>	17.27 mm   0.68 in
<b>Depth</b>	177.8 mm   7 in

## Optical Specifications

<b>Starting Wavelength</b>	1611 nm
----------------------------	---------

Packaging and Weights

**Packaging quantity** 1

Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

