329595-000 | GELSNAP-B-14/5-130-INT



GELSNAP Copper Closure, unpressurized, gel sealed, butt/in-line, for up to 10 pair splices

- Prevents water ingress by use of non-flowing gel under permanent compression
- Robust and reliable under a wide variety of environmental conditions
- Butt, in-line, and branch configurations with many connector types are possible

Product Classification

Regional Availability EMEA

Product Type Gel filled closure

Product Series GELSNAP

General Specifications

Cable Sealing Type Gel filled

Closure Style In-line | Single-ended

Color Black

Splicing Capacity, maximum 10

Dimensions

 Height
 33 mm | 1.299 in

 Width
 80 mm | 3.15 in

 Length
 290 mm | 11.417 in

 Single Cable Diameter, maximum
 14 mm | 0.551 in


 Single Cable Diameter, minimum
 5 mm | 0.197 in

 Sheath Opening, nominal
 130 mm | 5.118 in

Dimension Drawing



329595-000 | GELSNAP-B-14/5-130-INT



Environmental Specifications

Environmental Space Aerial | Buried

Packaging and Weights

Included Gel compression springs | Gel-filled half-shells | Installation instruction | Strain relief

accessories | Tie wraps

Packaging quantity

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Classification
Below maximum concentration value
Designed, manufactured and/or distributed under this quality management system
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant
Compliant to this quality management practice
Compliant



