

# C100-BNFMR

## Base Product

CNT-100 CNT® Jumper with interface types N Female Bulkhead and MCX Male Right Angle, variable length



## Product Classification

<b>Product Type</b>	Braided cable assembly
<b>Product Brand</b>	CNT®
<b>Product Series</b>	CNT-100

## General Specifications

<b>Body Style, Connector A</b>	Bulkhead
<b>Body Style, Connector B</b>	Right angle
<b>Cable Family</b>	CNT-100
<b>Interface, Connector A</b>	N Female
<b>Interface, Connector B</b>	MCX Male
<b>Orientation</b>	0°
<b>Specification Sheet Revision Level</b>	A
<b>Variable Length</b>	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

## Dimensions

<b>Length</b>	0 m   0 ft
<b>Nominal Size</b>	0.100 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.433	14.99

## Jumper Assembly Sample Label

# C100-BNFMR



## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system

## Included Products

100PMR-CR

- MCX Male Right Angle for CNT-100 braided cable

CNT-100-FR

- CNT-100-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket