

7640450-00



ION® Alarm Cable for Active Intelligent Point of Interface, 0.7 m inter-subrack connection

Product Classification

Product Type	Alarm cable
Product Brand	ION®

General Specifications

Cable, quantity	4
Connector A	Crimped dc connector, female, 4 contacts
Connector B	Crimped connector, female, 4 contacts
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.

Dimensions

Height	200 mm 7.874 in
Width	10 mm 0.394 in
Depth	250 mm 9.843 in
Cable Gauge	24 AWG

Electrical Specifications

Current per Pin	0.5 A
Electrical Safety Standard	EN 60950
Voltage Range	+5 to +60 Vdc

Packaging and Weights

Height, packed	250 mm 9.843 in
Width, packed	20 mm 0.787 in
Depth, packed	300 mm 11.811 in

7640450-00

Weight, gross 0.5 kg | 1.102 lb

Weight, net 0.25 kg | 0.551 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system