



6-to-1 Unit Splitter, for outdoor cable diameter of 0.41 in

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | SYSTIMAX® |
| Product Type | Unit splitter kit |
| Ordering Note | Order B sealant separately |

General Specifications

| | |
|-----------------------------|--------------------------|
| Color | Black |
| Compatible Interface | LC LC, keyed SC ST |

Dimensions

| | |
|---------------|--------------------|
| Height | 8.128 mm 0.32 in |
| Width | 20.32 mm 0.8 in |
| Length | 50.8 mm 2 in |

Material Specifications

| | |
|----------------------------|---------------------------------------|
| Material Type, body | Acrylonitrile butadiene styrene (ABS) |
|----------------------------|---------------------------------------|

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
|------------------------------|--------------------------------------|

Packaging and Weights

| | |
|---------------------------|---|
| Included | Six unit splitter Split tube seal Syringe |
| Packaging quantity | 1 |

Regulatory Compliance/Certifications

| | |
|---------------|--|
| Agency | Classification |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



