

760252850D | 20" Multi Carrier Integrated Pole, 13.5' Tall Base



Multi Carrier Round 20 inch diameter, Integrated Pole Base Concealment Pole for 4G/5G deployments, to house and conceal multiple radios and any other wireless infrastructure equipment in the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low to mid power 4G/5G outdoor small cell site
- Concealment integrates AC load center/OVP and disconnect

Radio Bracket Mounting Kits ordered separately:

- MTM1160-1101-AMK-E – Ericsson Radio Bracket Kit
- MTM1160-1101-AMK-N – Nokia Radio Bracket Kit
- MTM1160-1101-AMK-S – Samsung Radio Bracket Kit
- MTM1160-1101-AMK-H – CommScope Cap-H Radio Bracket Kit (Multi-tenant 'D-Module' ONLY)

Product Classification

Portfolio	CommScope®
Product Type	Integrated pole
Product Brand	Metro Cell
Ordering Note	CommScope® standard product with terms
Warranty	One year

General Specifications

Antenna Compatibility, CommScope	CommScope Canister Antennas
Antenna Compatibility, Other Vendors	ACE AMPHENOL GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERG
Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Co 6005) Metallic Silver Signal Black (RAL 9004) Umbra Grey (RAL 7022) White (RAL 9010)
Compatible Smart Devices	Cameras Digital Signage Emergency Call Station Environmental Monitoring Security Lighting
Cooling	Fan Cooling
Power Supply Compatibility	6304 ABB CC1600 CCI PSU-1200W-48-N DELTA 2.0 DELTA 3.0 PSU-AC-08
Radio Compatibility, Ericsson	1281 220x 440x 4415 4426 4435 4449 4478 6701 6705 8843 886
Radio Compatibility, Nokia	AEWB AEWD/AEWE AHFIA AHFIB AHFIC AHIA AHIB AWHHF AWHQN AZ

760252850D | 20" Multi Carrier Integrated Pole, 13.5' Tall Base

micro | Diplexer | Power Distribution

Radio Compatibility Samsung

AT1K01 | AT1K02 | DELTA 2.0 | Diplexer | Power Distribution | RF4402D-D1A | RT2201-46A

Radios Included

None

Dimensions

Height

4,114.8 mm | 162 in

Height Note

10 ft tall Equipment Base | 3.5 ft tall Radio Expansion Module

Pole Height Options

10.668 m | 35 ft | 12.192 m | 40 ft | 6.096 m | 20 ft | 7.62 m | 25 ft | 9.144 m | 30 ft

Width

508 mm | 20 in

Depth

508 mm | 20 in

Depth Note

Round

Pole Diameter

203.2 mm | 8 in

Electrical Specifications

Power/Fiber Input

AC load center with OVP and disconnect

Material Specifications

Finish Aluminum

Chromate

Finish Concealment Covers

Powder coated

Material Type

Steel

Environmental Specifications

Thermal Compliance

GR-487

* Footnotes

Warranty

For more information, please consult our Product Warranty guidelines

Pole Height Options

Overall AGL Standard Height