

296537-000 | OCM1-CA2511L2



OCM1 LGX Fiber Optic Module, CWDM, Mux/Demux, LC/APC, 2 channels, starting wavelength 1510 nm

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	CWDM module
Product Series	LGX OCM1

General Specifications

Device Type	Standard VAM
Functionality	Demultiplexing Multiplexing
Technology Type	Thin film filter (TFF)
Application	For use with LGX panels
Circuits, quantity	1
Distribution Type	2-channel CWDM
Interface, front	LC/APC
Interface, Input	LC/APC
Interface, Output	LC/APC
Multiplexers, quantity	1

Dimensions

Height	129.54 mm 5.1 in
Width	27.94 mm 1.1 in
Depth	127 mm 5 in

Optical Specifications

Channel Spacing	20 nm
Starting Wavelength	1510 nm

Packaging and Weights

Packaging quantity 1
Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

