



OCM1 LGX Fiber Optic Module, DWDM, Mux, SC/UPC, 8 channels, upgrade port, starting wavelength 1553.33 nm

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	DWDM module
Product Series	LGX OCM1

General Specifications

Device Type	Standard VAM
Functionality	Multiplexing
Application	For use with LGX panels
Circuits, quantity	1
Distribution Type	8-channel DWDM
Interface, front	SC/UPC
Interface, Input	SC/UPC
Interface, Output	SC/UPC
Multiplexers, quantity	1
Port Type, optional	Upgrade port

Dimensions

Height	129.54 mm 5.1 in
Width	58.42 mm 2.3 in
Depth	127 mm 5 in

Optical Specifications

Channel Spacing	100 GHz
Starting Wavelength	1,553.33 nm

Packaging and Weights

Packaging quantity 1
Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant/Exempted

