

# EHD-4U-W



SYSTIMAX® EHD 4U sliding tray fiber panel, accepts (24) EHD ULL modules, splice cassettes or MPO panels, providing up to 288 duplex LC ports or up to 288 MPO ports, white, High Speed Migration

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	EHD

## General Specifications

<b>Application</b>	Accepts 24 EHD Universal Modules, or EHD MPO adapter packs
<b>Color</b>	White
<b>Interface, front</b>	Unloaded
<b>Rack Units</b>	4
<b>Shelf Movement</b>	Sliding
<b>Total Ports, quantity</b>	0

## Dimensions

<b>Height</b>	177.8 mm   7 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	538.48 mm   21.2 in

## Packaging and Weights

<b>Weight, net</b>	15.604 kg   34.4 lb
--------------------	---------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

# EHD-4U-W

---

UK-ROHS

Compliant

