



RapidFiber® Faceplate, pull & click SC/APC, 30 meters cable on spool, wall mount

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Fiber wall outlet, with cable
<b>Product Brand</b>	RapidFiber®
<b>Product Series</b>	RFP

## General Specifications

<b>Color</b>	White
<b>Cover Type</b>	Hinged with latches
<b>Interface Type</b>	SC/APC
<b>Mounting</b>	Wall mount
<b>Port Capacity, maximum</b>	2
<b>Total Ports, quantity</b>	1

## Dimensions

<b>Height</b>	74.93 mm   2.95 in
<b>Width</b>	115.062 mm   4.53 in
<b>Depth</b>	52.07 mm   2.05 in
<b>Cable Length</b>	30 m   98.425 ft
<b>Cable Diameter</b>	1 mm   0.039 in

## Material Specifications

<b>Material Type</b>	LSZH thermoplastic
----------------------	--------------------

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.657.B3

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)  
**Environmental Space** Indoor

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant/Exempted

