

Constellation™ Powered Backplane

Product Classification

Regional Availability	North America
Portfolio	SYSTIMAX®
Product Type	Backplane
Product Brand	Constellation™

General Specifications

Color	Putty white
--------------	-------------

Dimensions

Height	256 mm 10.079 in
Width	560.8 mm 22.079 in
Depth	166.8 mm 6.567 in
Length	166.8 mm 6.567 in

Electrical Specifications

Input Voltage	100–120 Vac 36–56 Vdc
Output Current, maximum	3 A
Output Voltage	336 Vdc

Material Specifications

Material Type	Powder coated steel
----------------------	---------------------

Environmental Specifications

Operating Temperature	-20 °C to +50 °C (-4 °F to +122 °F)
Storage Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Relative Humidity	5%–95%, non-condensing
Environmental Space	Indoor
Safety Standard	IEC 62368-1

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

