

SSH-2630



SnapTak PIM-Guard Adjustable Hanger, Gen 2. Fits 26.0 mm to 30.0 mm Cables – PIM Free Polymer Construction. No Grommets Required.

Product Classification

Product Type	Hanger kit
Product Brand	SnapTak PIM-Guard
Ordering Note	CommScope® standard product (Global)

General Specifications

Accessories	Hangers
Cables per Hanger	1
Color	Black
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder

Dimensions

Maximum Stack Height	3
Maximum Stack Height, Coaxial	3
Height	67.23 mm 2.647 in
Width	42 mm 1.654 in
Length	77.29 mm 3.043 in
Compatible Cable Diameter Range	26–30 mm
Compatible Diameter, maximum	30 mm 1.181 in
Compatible Diameter, minimum	26 mm 1.024 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

SSH-2630

Material Specifications

Material Type Engineered plastic

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥1000 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 4.5 cm | 1.772 in

Width, packed 20 cm | 7.874 in

Length, packed 30 cm | 11.811 in

Packaging quantity 10

Weight, gross 0.36 kg | 0.794 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power