





HELIAX® Hangers: Vendor and product agnostic

CommScope HELIAX® hangers work with a variety of power, fiber, hybrid, and data applications. To find the right hanger for your build, match any applicable cable's outside jacketing diameter with the ranges in the table below.

					
OD Range mm	Cable OD mm	SnapTak® (PIM-Guard™)	SnapStak® (stainless steel)	Single Cable Grommets, used with SnapStak or Block Hangers (example SSH-12 & BCU12 accommodate cables 5-12mm)	CLICK Hanger Blocks (double cables)
5-11	5.00	SSH-411	N/A	SSH-12 + BCU12 or HG-5MM-12 SSH-78 + BCU78	N/A
	5.10				
	5.40				
	5.40				
	6.00				
	7.00				
	7.37				
	7.37				
	8.00				
	8.00				
11-20	10.28	SSH-1117	N/A	SSH-12 + BCU12 or HG-10MM-12 SSH-78 + BCU78 or HG-38-78 SSH-114 + HG-38-114	912MCLICK
	10.92				
	11.02				
	11.13				
	11.68				
	12.95				
	13.46				
	15.37				
	15.75				
	15.88				
20-30	16.43	N/A	SSH-M	SSH-78 + BCU78	N/A
	18.31				
	18.31				
	18.31				
	20.12				
30-42	23.36	SSH-2630	SSH-M	SSH-78 + HG-23MM-78 SSH-114 + BCU114 or HG-24-114 SSH-158 + BCU158	1316MCLICK
	25.81				
	27.99				
	27.99				
42-44	30.23	SSH-3642	SSH-78	SSH-114 + HG-27MM-114 SSH-158 + BCU158 or HG-2431-158	L5CLICKB
	39.40				
	39.62				
50-51	39.62	N/A	SSH-XL	SSH-158 + BCU158 or HG-2431-158	N/A
	44.70				
50-51	44.70	N/A	SSH-XL	SSH-158 + HG-44MM-158	N/A
	50.80				
50-51	51.05	N/A	SSH-158 SSH-XL	N/A	L7CLICK
	51.05				

commscope.com

Visit our website or contact your local CommScope representative for more information.

© 2024 CommScope, LLC All rights reserved.

CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see <https://www.commscope.com/trademarks>. All product names, trademarks and registered trademarks are property of their respective owners.

CO-118742.1-EN (04/24)

To learn more about HELIAX hangers and other accessory solutions from CommScope, contact your local representative today!