# ATCB-B01-003



Product Classification	
Product Type	AISG standard cable
General Specifications	
AISG Connector A	8-pin DIN Female
AISG Connector A Body Style	Straight
AISG Connector A Standard	IEC 60130-9
AISG Connector B	8-pin DIN Male
AISG Connector B Body Style	Straight
AISG Connector B Standard	IEC 60130-9
Color	Black
Data Conductor Type	0.24 mm² (24 AWG) twisted pair
EU Certification	CB   CE
Power Conductor Type	0.82 mm² (18 AWG) stranded
Total Conductors, quantity	6
Dimensions	
Length	3 m   9.843 ft
Diameter Over Jacket	8 mm   0.315 in
Electrical Specifications	

Protocol	AISG 1.1	AISG 2.0
Voltage, maximum	300 V	

#### Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 100%

AISG RET Control Cable, 3 m

- Feeds data and power to RET system components
- AISG and RoHS compliant

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 28, 2023



# ATCB-B01-003

Climatic Sequence Test Method	IEC 60068-2-14
Cold Exposure Test Method	IEC 60068-2-1
Damp Heat Exposure Test Method	IEC 60068-2-30, Test Condition Db
Heat Exposure Test Method	IEC 60068-2-2
Ingress Protection Test Method	IEC 60529:2001, IP67
Rain Simulation Test Method	IEC 60068-2-18, Test Condition Ra, Method 1
UV Resistance Test Method	IEC 60068-2-5, Test Condition B

#### Packaging and Weights

Weight, net

0.3 kg | 0.661 lb

### Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant
(())	



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 28, 2023

**COMMSCOPE**°