



#### **Product Classification**

Product Type Braided coaxial cable

Product Brand CNT®
Product Series CNT-400

#### General Specifications

Braid Coverage90 %Cable TypeCNT-400Jacket ColorBlack

#### **Dimensions**

 Diameter Over Dielectric
 7.24 mm | 0.285 in

 Diameter Over Jacket
 10.29 mm | 0.405 in

 Diameter Over Tape
 7.391 mm | 0.291 in

 Inner Conductor OD
 2.74 mm | 0.108 in

 Outer Conductor OD
 8.08 mm | 0.318 in

Nominal Size 0.400 in

#### **Electrical Specifications**

Cable Impedance 50 ohm

**Capacitance** 78 pF/m | 23.774 pF/ft

dc Resistance, Inner Conductor4.69 ohms/km | 1.43 ohms/kftdc Resistance, Outer Conductor5.61 ohms/km | 1.71 ohms/kft

dc Test Voltage  $2500 \ \lor$  Jacket Spark Test Voltage (rms)  $4000 \ \lor$ 



## CNT-400

Maximum Frequency 16.2 GHz

Operating Frequency Band 30 - 6000 MHz

Peak Power16 kWShielding Effectiveness90 dBVelocity85 %

#### Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
30.0	2.49	0.76
50.0	3.18	0.97
150.0	4.92	1.5
220.0	6.23	1.9
450.0	8.86	2.7
900.0	12.8	3.9
1500.0	16.7	5.1
1800.0	18.4	5.6
2000.0	19.4	5.9
2400.0	21.65	6.6
2500.0	22	6.7
3000.0	24.6	7.5
4000.0	28.87	8.8
4500.0	30.84	9.4
5000.0	32.81	10
5200.0	33.46	10.2
5500.0	34.78	10.6
5800.0	35.76	10.9
6000.0	36.42	11.1

## Material Specifications

Braid Material Tinned copper
Dielectric Material Foam PE

Jacket Material Non-halogenated PE

Inner Conductor Material Copper-clad aluminum wire

Shield Tape Material Aluminum

# CNT-400

## Mechanical Specifications

Minimum Bend Radius, single Bend25.4 mm | 1 inTensile Strength73 kg | 160.937 lbBending Moment0.7 N-m | 6.196 in lbFlat Plate Crush Strength0.7 kg/mm | 39.198 lb/in

## **Environmental Specifications**

Installation temperature-40 °C to +85 °C (-40 °F to +185 °F)Operating Temperature-40 °C to +85 °C (-40 °F to +185 °F)Storage Temperature-70 °C to +85 °C (-94 °F to +185 °F)

Packaging and Weights

**Cable weight** 0.1 kg/m | 0.067 lb/ft

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant





